

VeroUltra for Stratasys J55

VeroUltra™ includes VeroUltra™ WhiteS and VeroUltra™ BlackS colors and is available for the J55 printer. VeroUltra™ is available in 1.1 kg cartridges for the J55 printer. The use of VeroUltra™ WhiteS and VeroUltra™ BlackS improves significantly the color opacity and color uniformity. It also provides a smoother texture enabling high quality plastic appearance, ultra-sharp graphics and high contrast print levels previously impossible to achieve.

Opaque materials facilitate the printing of thin parts, providing richer colors with sharper textures and texts. Opaque shades bring models to life with un-matched color realism.

Vero Opaque for J55

VeroUltra™ WhiteS (RGD824), VeroUltra™ BlackS(RGD864) available in 1.1 kg cartridges

Vero Opaque Family for J55

	ASTM	Value
Tensile Strength	D-638-03	50-65 (7250-9430 psi)
Elongation at Break	D-638-05	5-20 %
Modulus of Elasticity	D-638-04	2000 - 3000 MPa (290000 - 435000 psi)
Flexural Strength	D-790-03	65-85 (9400-12300 psi)
Flexural Modulus	D-790-04	2000-2800 (290000-406100 psi)
HDT, °C @ 0.45MPa	D-648-06	48-52 °C (118-126 °F)
HDT, °C @ 1.82MPa	D-648-07	44-47 °C (111-117 °F)
Izod Notched Impact	D-256-06	20-30 J/m (0.375 – 0.562 ft-lb/in.)
Water Absorption	D-570-98 24hr	1.1-1.4%
Tg	DMA, E>	54-56 °C (124-133 °F)
Shore Hardness (D)	Scale D	83 – 86
Polymerized Density	ASTM D792	1.19-1.23

System Availability

Printer	Min Layer Thickness	Support Structure	Available Colors
J55	18 microns (0.0007 in.)	SUP710 (WaterJet removable)	VeroUltra™ WhiteS VeroUltra™ BlackS

Stratasys Headquarters

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

stratasys.com

ISO 9001:2015 Certified

