



Digital ABS Plus

POLYJET SIMULATED ABS PLASTIC

Digital ABS Plus™ is designed to simulate standard ABS plastics by combining high-temperature resistance with toughness. Suitable for parts that require PolyJet™ technology's highest possible impact resistance and shock absorption, Digital ABS Plus significantly improves the mechanical performance of parts and prototypes for design verification and functional performance testing. Get better impact strength with high-temperature resistance, toughness and superior finish. Digital ABS Plus is ideal for rapid prototyping snap-fit parts for high or low temperature use, functional designs with multi-material versatility and flexibility, molds, manufacturing tools, electrical parts and more.



LEARN ABOUT DIGITAL ABS PLUS AT [STRATASYS.COM](https://www.stratasys.com)

stratasys

A GLOBAL LEADER IN APPLIED ADDITIVE TECHNOLOGY SOLUTIONS



Digital ABS Plus

POLYJET SIMULATED ABS PLASTIC

At the core:

PolyJet Technology

PolyJet technology creates precise prototypes that set the standard for finished-product realism. Its fine resolution makes complex shapes, intricate details and smooth surfaces possible. PolyJet 3D Printing works by jetting layers of liquid photopolymer onto a build tray and instantly curing them with UV light. The fine layers build up to create a precise 3D model or prototype. Models are ready to handle right out of the 3D printer, with no post curing needed.

Keep valuable resources in-house

You'll be amazed when you see how easy it is to produce realistic models in-house. PolyJet 3D Printers offer not only unparalleled speed, they make it easy for you to print with the widest range of material properties.

No special facilities needed

You can install PolyJet 3D Printers just about anywhere. No special venting is required because PolyJet 3D Printers don't produce noxious fumes, chemicals or waste.

Good ideas sell easier

PolyJet 3D Printers improve communication and collaboration because they produce amazingly accurate representations of your ideas that you can share with your team and your clients for a faster, more confident buy-in.

MECHANICAL PROPERTIES	TEST METHOD	IMPERIAL	IMPERIAL METRIC
Tensile Strength	D-638-03	8,000-8,700 psi	55-60 MPa
Elongation at Break	D-638-05	25-40%	25-40%
Modulus of Elasticity	D-638-04	375,000-435,000 psi	2,600-3,000 MPa
Flexural Strength	D-790-03	9,500-11,000 psi	65-75 MPa
Flexural Modulus	D-790-04	245,000-320,000 psi	1,700-2,200 MPa
HDT, °C @ 0.45MPa	D-648-06	136-154 °F	58-68 °C
HDT, °C @ 0.45MPa after thermal post treatment procedure A	D-648-06	180-194 °F	82-90 °C
HDT, °C @ 0.45MPa after thermal post treatment procedure B	D-648-06	198-203 °F	92-95 °C
HDT, °C @ 1.82MPa	D-648-07	124-131 °F	51-55 °C
Izod Notched Impact	D-256-06	1.69-2.15 ft lb/in	90-115 J/m
Tg	DMA, E>	117-127 °F	47-53 °C
Shore Hardness (D)	Scale D	85-87 Scale D	85-87 Scale D
Rockwell Hardness	Scale M	67-69 Scale M	67-69 Scale M
Polymerized Density	ASTM D792		1.17-1.18 g/cm ³

SYSTEM AVAILABILITY	LAYER THICKNESS CAPABILITY	SUPPORT STRUCTURE	AVAILABLE COLORS
Objet260/350/500 Connex3™ Stratasys J750™ Objet1000 Plus™		SUP705 (WaterJet removable) SUP706* (soluble)	Green (RGD515 Plus and RGD535) Ivory (RGD515 Plus and RGD531)

* Not compatible with Objet1000 Plus or HQ mode for Stratasys J750.

stratasys

STRATASYS.COM
ISO 9001:2008 Certified

HEADQUARTERS

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937 3000 (Intl)
+1 952 937 0070 (Fax)

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)