

# Stratasys J4100

**Create large or small production tools and full-scale prototypes.**

Maximize your productivity and quickly achieve ROI with the Stratasys J4100™ 3D Printer. Its multimaterial capabilities, substantial throughput and ultra-large build tray help get jobs done faster, smarter and with more precision. Driven by PolyJet Technology™, this powerful system enables engineers, manufacturers and designers to 3D print any design – no matter how complex or detailed.

Part size is no object: the J4100 is equally adept at printing large or small prototypes with no compromise on precision. In one build, print large parts over one meter in length, eliminating the need to split large files in CAD and bond parts later. Print many parts in one job and enjoy a competitively low cost per part.

Reliable and easy to use, the J4100 helps you build parts that are ready for use with little or no post-processing. Support material is quick to remove with a WaterJet, and for most applications the smooth, multi-material parts require no polishing or painting

## 3D Printer Specifications

Model Materials	Neutral shades	Flexible materials
	<input type="checkbox"/> VeroPureWhite™	■ Agilus30 Black
	■ VeroBlackPlus™	<input type="checkbox"/> Agilus30 Clear
	■ VeroBlue™	Digital materials
	■ VeroGray™	■ Digital ABS Plus™ Ivory
	Transparent materials	■ Digital ABS Plus™ Green
	<input type="checkbox"/> VeroClear™	
	<input type="checkbox"/> VeroUltraClear™	
Support Materials	SUP705™ (WaterJet removable)	
Build Size	1000 x 800 x 500 mm (39.4 x 31.5 x 19.7 in)	
Layer Thickness	Horizontal build layers range between 27 microns - 55 microns (0.001 in. - 0.002 in.) depending on the print mode.	
Workstation Compatibility	Windows 7	
Network Connectivity	LAN – TCP/IP	
System Size and Weight	1960 x 2868 x 2102 mm (77.5 x 113 x 83 in.) 2200 kg (4850 lbs.)	
Operating Conditions	Temperature 18 – 25 °C (64 – 77 °F); relative humidity 30-70% (non-condensing)	
Power Requirements	230 VAC 50/60 Hz, 8A single phase	
Regulatory Compliance	CE, FCC	
Software	GrabCAD Print™ with Advanced Slicer	
Build Modes	High Speed: up to 3 base resins, 27 micron (0.001 in.) resolution Super High Speed: 1 base resin, 55 micron (0.002 in.) resolution	
XY Resolution	300x600 DPI	



### Stratasys Headquarters

7665 Commerce Way,  
Eden Prairie, MN 55344  
+1 800 801 6491 (US Toll Free)  
+1 952 937-3000 (Intl)  
+1 952 937-0070 (Fax)

[stratasys.com](http://stratasys.com)

ISO 9001:2015 Certified

1 Holtzman St., Science Park,  
PO Box 2496  
Rehovot 76124, Israel  
+972 74 745 4000  
+972 74 745 5000 (Fax)

