TECHSTYLE


Discover the magic of 3DFashion



stratasys | J850 TechStyle

Limitless Creativity

The Stratasys TechStyle[™] 3D printer is making waves with its revolutionary 3DFashion[™] printing technology. For the first time ever, 3D algorithms can be printed direct-to-textile, creating fascinating illusions with color and light. Parametric design, computed 3D design and aesthetics can now be created by a computer-generated design flow, that cannot be completed manually. In an industry where it was once not possible, TechStyle enables fashion designers to truly unleash their imagination with limitless creations and unparalleled flexibility through a wide range of rigid and flexible materials. The multiple advantages over traditional forms of design enable the creation of fantastic optical illusionary effects, direct to textile and garments, in clear print and in full color.



3D Kimono "WeAreAble" collection By **Ganit Goldstein** in collaboration with STRATASYS (image above and image on cover)

Design Freedom

TechStyle 3D printer allows designers and high-end fashion brands a new level of design freedom, for personalization and customization, in low-volume production, with seamless integration and minimum downtime.

TechStyle has a virtually limitless color palette to choose from, with over 600K available colors and Pantone Validated[™] pallets in both matte and glossy finishes. Your required print area can be designated on a stretch of fabric up to 2m².

The printer's cabinet holds 7 cartridges for materials, from vivid colors to full transparency that will support any design, including textures with both rigid and flexible materials. Easily print with your favorite design software from the multitude of compatible options and output your file direct to GrabCAD[™] for printing.



Unparalleled Productivity

The vast array of colors and material properties, from rigid to flexible and opaque to transparent, will eliminate the need for multiple processes to create unique volumetric colorful designs on textile and garments. The J850 TechStyle's flexible printing capabilities are unmatched, with 2-mode capability that enables it to print directly onto textiles as well as used garments for repurposing. 3D models for fashion accessories, such as buttons, cufflinks and bag clips, can also be printed, to a maximum height of 50mm. This printer also features an interchangeable tray, so that during a print you can prepare a second tray and be ready to quickly switch for faster production runs and minimum down time. The unique Fabric Analyzer technology will analyze a fabric sample for digital design optimization, obliterating the need to waste time and costs on multiple iterations prior to production. An exclusive Print on Existing Patterns process will allow you to 3D print on predefined patterns within a fabric such as stars, polka dots etc.

J850™ TechStyle™ Direct-to-textile, multi-material, full color 3D printer

Efficient Workflow

Streamline your workflow with GrabCAD Print software by printing directly from your favorite professional CAD formats, with the addition of advanced rendering software. Eliminate time-consuming painting or trial-anderror Pantone color matching with a single-click step in GrabCAD Print. Use smart default settings, tooltips, and notifications to guide you through a seamless printing process. Work with detailed views of your model, tray and slice preview so you can make any necessary adjustments before going to print. The large, seven-material capacity of the Stratasys J850 TechStyle printer means you can load your most used resins and avoid downtime associated with material changeovers. GrabCAD Print software is an Industry 4.0 compatible system that will fully integrate with manufacturing execution systems (MES) and your digitized production floor.



Sustainable Manufacturing

Stratasys J850 TechStyle 3D printer promotes mindful manufacturing and low volume production, while eradicating oversupply and reducing unnecessary waste. As a founding member of the Additive Manufacturer Green Trade Association, Stratasys TechStyle eliminates the need for excessive inventories, while used clothing and accessories can be repurposed with the addition of 3D printed elements.

Responsible consumption, industry innovation and revised supply chains go hand-in-hand with 3D printing technologies. This enables designers to generate full color, intricate designs, in-house, that can't be achieved through other processes. This is fashion forward; 3D Printing a better tomorrow, today.



All The Specs You Need

Product Specifications					
Model Materials	 Vero[™] & VeroUltra[™] family of opaque materials + neutral shades and vibrant VeroVivid[™] colors Agilus30[™] Clear, Black, White, Cyan, Magenta, Yellow Transparent VeroClear[™] and VeroUltra[™]Clear Vero[™]ContactFlex for soft touch model coating 				
	Unlimited number of digital materials includin	g:			
Digital Model Materials	 Over 600,000 colors and Pantone[®] Validated pal Translucent color tints Flexible tactile materials in a variety of textures ar 				
Support Materials	SUP705 [™] (water jet removable) SUP706B [™] (soluble)				
Printed Textile Testing*	ISO standards	100% Cotton	100% Polyester	50/50% Cotton Polyester	Linen
	ISO 105-C06:2010 @40c (1-5)	5	5	5	5
	ISO 105-C06:2010 @60c (1-5)	5	5	5	5
	ISO 105-B02:2013 (1-8)	7-8	7-8	7-8	7-8
Build Size	Fabric Size Handling: min 560 x 460mm; max 2	x 2m			
	Fabric Thickness: 0.1-3.0mm				
	Interchangeable Tray for smooth production runs				
Effective Printing Area	460 x 360 x 50 mm (18.1 x 14.2 x 1.9 in) on a stretch of fabric up to $2m^2$				
Layer Thickness	Horizontal build layers down to 27-micron (0.001 in.)				
Workstation Compatibility	Windows 10				
Network Connectivity	LAN - TCP/IP				
	Industry 4.0 Compliance				
System Size and Weight	J850 TechStyle System:				
	1400 x 1260 x 1100 mm (55.1 x 49.6 x 43.4 in.); 430 kg (948 lbs.)				
	J850 TechStyle Material Cabinet:				
	1119 x 656 x 637 mm (44 x 25.8 x 25.1 in.); 153 kg (337 lbs.)				
Operating Conditions	Temperature 18 – 25 °C (64 – 77 °F); relative humidity 30-70% (non-condensing)				
Power Requirements	100–120 VAC, 50–60 Hz, 13.5 A, 1 phase; 220–240 VAC, 50–60 Hz, 7 A, 1 phase				
Regulatory Compliance	CE, FCC, EAC, RCM, R-NZ1				
Software	GrabCAD Print, SDK (API)				
Build Modes	High Mix: up to 7 base resins, 27-micron (0.001 in.) resolution				
	High Speed: up to 3 base resins, 27-micron (0.001 in.) resolution				
Accuracy	J850 TechStyle System: Typical deviation from STL dimensions, for models printed with rigid materials, based on size: under 100 mm – \pm 100µ; above 100 mm – \pm 200µ or \pm 0.06% of part length, whichever is greater.				
	Print on Existing Patterns: up to 1mm				
	Software: Deviation from STL dimensions, for 1 Sigma (67%) of models printed with rigid materials, based on size: under 100 mm $- \pm 150\mu$; above 100 mm $- \pm 0.15\%$ of part length.				
	Deviation from STL dimensions, for 2 Sigma (95%) of models printed with rigid materials, based on size: under 100 mm – \pm 180µ; above 100 mm – \pm 0.2% of part length.				

TechStyle

Discover the magic of 3DFashion

Stratasys Headquarters

7665 Commerce Way, Eden Prairie, MN 55344 +1 800 801 6491 (US Toll Free) +1 952 937-3000 (Intl) +1 952 937-0070 (Fax)

stratasys.com

ISO 9001:2015 Certified

© 2022 Stratasys Ltd. All rights reserved. Stratasys, Stratasys signet J850, TechStyle, 3DFashion, GrabCAD Print, Vero, VeroVivid, Agilus30, VeroClear, VeroUntaClear, VeroContactFlex, SUP705 and SUP706B, are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. PANTONE® and other Pantone trademarks are the property of Pantone LLC. Pantone's trademarks and copyrights used with the permission of Pantone LLC under License Agreement with Stratasys Ltd. All other trademarks belong to their respective owners. Product specifications subject to change without notice. BR_PJ_TechStyle_0322a

1 Holtzman St., Science Park,

PO Box 2496

Rehovot 76124, Israel +972 74 745 4000

+972 74 745 5000 (Fax)

