

Mission to Mars 3D printed transroporter supports SPACE EXPLORATION

"We decided to 3D print the TransRoPorter prototype, which offered us the least expensive, fastest and most elegant solution. Everyone involved in the project is delighted with the outcome."

> Dr. Kaj Fuehrer, Head of System Building Technology South

CASE STUDY



TransRoPorter Prototype with FDM 3D printed components.

Mars, the mysterious red planet, has always been a fascination. Over 40 space probes have already been sent to Mars, but the question still remains; does life exist on our neighboring planet? The unmanned flight to Mars has been a long-term goal of several leading space agencies. Most notably NASA and its space shuttle 'Orion', the European Space Agency (ESA) with program 'Aurora' and the Russian Space Agency 'Roskosmos,' while India and China also join this reputable contingent.



At the German Aerospace Center (Deutsches Zentrum für Luft- und Raumfahrt e.V. (DLR)) in Oberpfaffenhofen, the exploration of Mars is also a hot topic. Acting on behalf of the German government within the national space program, the German Aerospace Center is responsible for research and contributions to the ESA and tasked with developing long-term research goals for the state. At the Institute for Robotics and Mechatronics (Institut für Robotik und Mechatronik), a division of the German Aerospace Centre (DLR), researching the latest technologies to advance space exploration is an important part of achieving the goals of a mission.

Producing complex prototypes for extreme environments

Working in close collaboration with the Institute for Robotics and Mechatronics is Dr. Kaj Fuehrer, Head of System Building Technology South (Leiter Systemhaus Technik Sued) at DLR. The System Building Technology function serves as a point of contact for the research team, providing them expertise in implementing technology within research projects. Acting as an advisory body, Dr. Fuehrer and his team are extremely knowledgeable when it comes to design and production with varying manufacturing methods. "Our prototypes are often very complex and typically push the boundaries of what is possible," says Dr. Fuehrer. "Therefore, it is important to choose the appropriate production method and material, so that we can achieve the desired functionality without any limitations."

When Dr. Fuehrer's colleagues, Dr. Stefano Seriani and Dr. Armin Wedler, approached him about the production of a prototype TransRoPorter (TRP) – an exploration robot for unmanned flights to Mars – the decision to use 3D printing was an easy one. The TransRoPorter is made from two components: the moveable TRP Rover-Unit, made to navigate in unstructured terrain, and the Payload Module (PM), which carries spare parts, communication technology and scientific tools. Rigorous testing is required to ensure functionality and practicality of the first prototypes of the TransRoPorter. As a result, DLR turned to Stratasys FDM[®] 3D Printing to test the design and functionality of the robot under simulated extreme conditions ahead of time. "The Payload Module is at the heart of the system, and we needed a fully-functional prototype that could perform in all tests and withstand the strain of the design," explains Stefano Seriani.

Dr. Fuehrer adds: "In the planning of this project, we always preferred 3D printing technology. For us it was clear, a prototype made from metal was too expensive and complex in production. A metal prototype would also need to be finished post-production, which means more work with additional costs. Therefore, we decided to 3D print the TransRoPorter prototype, which offered us the least expensive, fastest and most elegant solution. Everyone involved in the project is delighted with the outcome."

High-performance materials for fully-functional prototyping

Using a Stratasys Fortus 900mc[™] Production 3D Printer, the research team is 3D printing large parts in FDM thermoplastic materials. According to Dr. Fuehrer, the ASA material is ideally suited for testing the TransRoPorter prototype, enabling the team to produce a strong enough box to contain all the technology safely within. "It was extremely important that the fit was right, that the box could be mounted to the tracks and the docking port worked," he explained. "Utilizing Stratasys FDM



TransRoPorter Box printed on the Stratasys Fortus 900mc 3D Printer.



3D printing technology, we found that the material basically has no distortion. The decision for ASA material was consciously made, as it is ideal for our purposes and handling."

Stefano Seriani adds: "The stability of the ASA material also played a large role for us. We needed a fully functional prototype that could perform in all tests and withstand the strain of the design. The tough and rigid properties of the Stratasys material was therefore an ideal fit to test the TransRoPorter's functionality for its journey to Mars."

Gaining valuable knowledge

The TransRoPorter is currently set for launch in 2021/2022. Comprehensive functionality tests for the Payload Module are already being undertaken by the researchers to simulate if what's planned can be executed successfully or if the design of the prototype needs adjusting. The use of Stratasys 3D printing has supported other strategic goals. According to Dr. Fuehrer, the knowledge gained during the production of the TransRoPorter was just as important as ensuring its functionality.

He concluded, "A new technology leads to new thought processes. Over the past few years, many colleagues have started to think in 3D and are using 3D printing to plan other projects they are starting. This new knowledge has opened them up to a new set of possibilities within product development."



STRATASYS.COM

ISO 9001:2008 Certified

HEADQUARTERS

7665 Commerce Way, Eden Prairie, MN 55344 +1 800 801 6491 (US Toll Free) Rehovot 76124, Israel +1 952 937-3000 (Intl) +1 952 937-0070 (Fax)

2 Holtzman St., Science Park. PO Box 2496 +972 74 745 4000 +972 74 745 5000 (Fax)

© 2017 Stratasys. All rights reserved. Stratasys, FDM, Fortus, Fortus 900mc and ASA are trademarks of Stratasys, Inc. All other trademarks are the property of their respective owners, and Stratasys assumes no responsibility with regard to the selection, performance, or use of these non-Stratasys products. Product specifications subject to change without notice. Printed in the USA. CS_FDM_AE_GermanAerospaceCenter_0817a