

Bird's Eye View

FDM REDUCES THE TIME AND COST REQUIRED TO DEVELOP UNMANNED AERIAL VEHICLE

"It would not have been possible for a company of our size to design and build this product using conventional manufacturing methods."

- John Oakley, Leptron

CASE STUDY



The RDASS 4 unmanned aerial vehicle weighs only five pounds

Leptron is a leader in remotely piloted helicopters focusing on law enforcement, military and civilian uses. Leptron's RDASS 4 is a unique unmanned aerial vehicle (UAV) that weighs only five pounds and can be in the air in five minutes' notice. Its four battery-powered electric motors enable it to hover at 100 feet with a half-mile line of sight. The device carries a wide range of cameras and other electronic equipment.

A typical military application for the RDASS 4 is to provide an armored vehicle with the ability to see over the horizon and inspect terrain or structures that might present a danger. Computer simulation has shown that the device can increase survivability of an armored vehicle by 50%. The RDASS 4 also has many other applications including police work.



The fuselage of the RDASS 4 is constructed in a series of nested sections called layers that fit together similar to Russian dolls. The company has developed multiple designs for each layer for specific civilian and military applications. Each layer can be easily interchanged with the others to be tailored specifically to the needs of a particular application without substantial additional cost or delivery time.

When designing the RDASS 4, Leptron engineers faced the challenge of developing eight variations of complex fuselage components in a short period of time to beat potential competitors to market. The plastic components that form the shell for the layers must withstand functional and crash tests where the RDASS 4 is flown into the ground. The craft must demonstrate the ability to be easily repaired and flown again after the crash. A minority of parts have mechanical requirements that cannot be met by plastic so they are made of metal.

Using the traditional approach, injection molding, it would have cost \$250,000 and taken six months to build tooling for these fuselage components. Another problem is that any design changes after the tooling was built would have required expensive and time-consuming modifications to the tooling. Major changes would have involved even greater costs and delays to build new tooling.

"We investigated various rapid prototyping technologies and discovered that the FDM process could provide components that met the mechanical requirements for all of our plastic fuselage components," said John Oakley, Chief Executive Officer of Leptron. Fused Deposition Modeling (FDM) technology is an additive manufacturing process that builds plastic parts layer by layer, using data from CAD files.

Leptron now uses the Dimension 3D Printer to very quickly build end use parts for the RDASS 4. The core components take 48 hours while smaller components average six hours to print. The printed parts are suitable for form and fit evaluation, functional testing and end use parts. Using the same Dimension machine for making prototype and end use parts reduces up-front investment and enables Leptron to build UAVs without a machine shop. The plastic parts needed for prototypes and eight production craft were built for only \$100,000 in eight months.

"We made approximately 200 design changes during the course of the project," Oakely said. "They included everything from reinforcing the structure to shoring up weak areas to making aerodynamic improvements. Every single part has changed a minimum of four times. FDM gave us the flexibility to make these changes without incurring a significant time or cost penalty. It would not have been possible for a company of our size to design and build this product using conventional manufacturing methods."



The RDASS 4 fits into a compact case for easy transport and fast deployment.



FDM electronic housing



FDM battery box



FDM bracket used to the legs of a UAV.

How Did Dimension 3D Printing Compare to Traditional Prototyping Methods for Leptron?

METHOD	COST	LEAD TIME
Injection molding with CNC machined tooling	\$250,000	14 months
FDM end use parts	\$103,000	8 months
Savings	\$147,000 (59%)	6 months (43%)



E info@stratasys.com / STRATASYS.COM

ISO 9001:2008 Certified

HEADQUARTERS

7665 Commerce Way, Eden Prairie, MN 55344 +1 888 480 3548 (US Toll Free) +1 952 937 3000 (Intl)

+1 952 937 0070 (Fax)

0070 (Fax)

2 Holtzman St., Science Park, PO Box 2496 Rehovot 76124, Israel +972 74 745-4000 +972 74 745-5000 (Fax)

©2015, 2013 Stratasys Inc. All rights reserved. Stratasys, Fortus, Dimension, uPrint and FDM are registered trademarks and Fused Deposition Modeling, FDM Technology are trademarks of Stratasys Inc., registered in the United States and other countries. All other trademarks are the property of their respective owners. Product specifications subject to change without notice. Printed in the USA. CS_FDM_AE_Leptron_EN_0915