

DraftGrey



DraftGrey™ is a rigid material within the Vero family of PolyJet™ resins used exclusively with Super High Speed print mode. DraftGrey allows users to print concept models twice as fast as High Speed Mode, for the fastest time-to-part on the J835™ and J850™ printers. Models made with DraftGrey have a medium opacity and a smooth finish.

	ASTM	Value
Tensile Strength	D-638-03	50 – 65 MPa (7,250 – 9,450 psi)
Elongation at Break	D-638-05	10 – 25%
Modulus of Elasticity	D-638-04	2,000 – 3,000 MPa (290,000 – 435,000 psi)
Flexural Strength	D-790-03	75 – 110 MPa (11,000 – 16,000 psi)
Flexural Modulus	D-790-04	2,200 – 3,200 MPa (320,000 – 465,000 psi)
HDT, °C @ 0.45 MPa	D-648-06	45 – 50 °C (113 – 122 °F)
HDT, °C @ 1.82 MPa	D-648-07	45 – 50 °C (113 – 122 °F)
Izod Notched Impact	D-256-06	20 – 30 J/m (0.375 – 0.562 ft-lb/inch)
Water Absorption	D-570-98 24hr	1.1 – 1.5%
Tg	D-7028 (DMA)	52 – 54 °C (126 – 129 °F)
Shore Hardness	Scale D	83 – 86 (Scale D)
Rockwell Hardness	Scale M	73 – 76 (Scale M)
Polymerized Density	Scale D-792	1.17 – 1.18 g/cm ³
Ash Content	USP281	0.23 – 0.26%

System Availability

Printer	Minimum Layer Thickness	Support Structure	Available Colors
J826™ / J835™ / J850™	14 microns	SUP705 (water jet removable) SUP706B (soluble)	DraftGrey

For information on the Draft Grey material properties on the J55™, please visit www.stratasys.com/3d-printers/j55.

Stratasys Headquarters

7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

stratasys.com
ISO 9001:2015 Certified

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

