




Neo[®]800+ 3D Printer

The new benchmark for high-speed, large-format SLA



Designed by Engineers, for Engineers.

The Neo[®]800+ 3D printer combines cutting-edge software and advanced technology to deliver up to **50% faster performance** than its predecessor. With enhanced part fidelity and reliability, it minimizes downtime and service needs, setting a new standard for large-format SLA printing with the **lowest total cost of ownership**.

System Specifications		
Laser & Scanning System	Laser	4 Watt, 355 nm, solid-state frequency tripled Nd:YVO ⁴
	Beam Focus	Dynamic & Variable
	Beam Size	120 to 750µm
	Scanning Speed	Up to 790 in./s (20 m/s)
Layer Resolution		50 to 200 µm*
Minimum Feature Size		0.007 in. (0.17 mm) in X & Y [†] 0.016 in. (0.4 mm) in Z [†]
Build Modes		High Detail & Standard Detail (HD & SD)
Accuracy		Dimension <3.94 in. ±0.004 in.; Dimension >3.94 in. ±0.15% [†] Dimension <100 mm ±0.1 mm; Dimension >100 mm ±0.15% [†]
Material Compatibility		Open resin system – compatible with commercially available 355 nm stereolithography resins
Capacities	Build (XYZ)	Half: 31.50 x 31.50 x 11.81 in. (800 x 800 x 300 mm) Full: 31.50 x 31.50 x 23.62 in. (800 x 800 x 600 mm)
	Vat Fill	Half: 83 US gal (780 lb [‡]) [316 ltr (354 kg [‡])] Full: 147 US gal (1,378 lb [‡]) [558 ltr (625 kg [‡])]
Software	Operating System	Windows 10 IoT Enterprise LTSC 2021
	Input File Format	SLC
	Control Software	Titanium
	Build Prep Software	GrabCAD or Materialise Magics
	Remote Editor	Titanium Assistant (optional)
Connectivity	Ethernet	Fully compliant with IEE 802.3, IEEE 802.3u, IEEE 802.3ab
	USB Port	USB 3.1
Features & Build Options		Build validation / Build time estimator / Material usage estimator / Scheduled start / Open build parameters enabling any material to be processed / On-the-fly parameter adjustment and part deletion / Upper surface build quality optimization / Bubble remover with automated option



System Specifications

Advanced Services & Reporting Tools		Industry 4.0 compliant / Full part traceability / Logging of machine utilization; build history; parameters; material usage; formatted data export / System and build status email notification [§] / Onboard camera / Resin viscosity tracking / User level access control / Scheduled lighting
Support		1-click "snapshot" job diagnostic pack for remote support / Remote diagnostics [§]
Electrical Requirements	208 - 240 V, 50/60 Hz	900 W Typical operation, 1,900 W Max
Environmental Requirements		Temperature range: 68 - 74 °F (20 - 23 °C), max rate change ±2 °F/hr (1 °C/hr) Relative humidity 20 - 50% non-condensing
UPS		1 - 2 hrs of system up-time with intelligent UPS control ^{***}
Dimensions (WxDxH)	Printer (uncrated)	53.2 x 64.2 x 90.6 in. (1,350 x 1,630 x 2,300 mm)
	Printer Crated	67.3 x 73.2 x 100.8 in. (1,710 x 1,860 x 2,560 mm)
	Vat (uncrated)	46.9 x 35.9 x 34.3 in. (1,190 x 910 x 870 mm)
	Vat Crated	55.2 x 41.4 x 43 in. (1,400 x 1,050 x 1,090 mm)
Weight	Printer	2,094 lb (950 kg)
	Vat	529 lb (240 kg)
Crated Weight	Printer	2,646 lb (1,200 kg)
	Vat	960 lb (435 kg)
Warranty	System	12 months on-site service and support, as per Stratasys conditions of sale
Accessories	UV800	1,058 lb (480 kg)
	Unload Cart	463 lb (210 kg)
Regulatory Conformity		

* 100µm layer parameters are supplied for Stratasys certified materials. Parameters for alternative thicknesses may be available. Layer thickness range is material dependent. Contact Stratasys for more details.

† Accuracy and minimum feature size will vary depending on material, parameters, part geometry and size, pre- and post-processing methods and environment.

‡ Based on typical material density, 2.47 lb/0.3 gal @ 78.8 °F (1.12kg/ltr @ 26 °C).

§ Internet connection is required for full or partial functionality.

** Specification can be subject to change without prior notice.

*** When connected to a Stratasys Certified UPS, not sold with the Neo800+ 3D printer, please contact Stratasys for further details.



stratasys.com

ISO 9001:2015

Certified

Stratasys Headquarters

5995 Opus Parkway,
Minnetonka, MN 55343
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

1 Holtzman St.

Science Park
Rehovot, 7670401
Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

PRODUCT SPEC SHEET

SLA

©2026 Stratasys. All rights reserved. Stratasys, the Stratasys Signet logo, Neo, Neo800, Neo800+, ScanControl+, Somos, PerFORM, WaterShed Black and WaterShed XC+ are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries and affiliates. All other trademarks are the property of their respective owners. PSS_SL_Neo800Plus_0526a