ABS-M30i



ABS-M30i is a high strength material well suited for the medical, pharmaceutical and food packaging industries. Parts manufactured with ABS-M30i material are biocompatible (ISO 10993 USP Class VI)* and can be gamma or EtO sterilized. When combined with Fortus® 3D Printers, ABS-M30i gives you biocompatible parts with excellent mechanical properties that are well suited for conceptual modeling, functional prototyping, manufacturing tools and production parts.

ABS-M30i is a high strength material well suited for the medical, pharmaceutical and food packaging industries. Parts manufactured with ABS-M30i material are biocompatible (ISO 10993)* and can be gamma or EtO sterilized. In addition, ABS M30i has passed ISO 18562 testing for gas and airway parts for use in respiratory and ventilation medical devices. When combined with Fortus® 3D Printers, ABS-M30i gives you biocompatible parts with excellent mechanical properties that are well suited for conceptual modeling, functional prototyping, manufacturing tools and production parts.

Mechanical Properties¹	Test Method	Value
Tensile Strength (Type 1, 0.125", 0.2"/min)	ASTM D638	36 MPa (4,650 psi)
Tensile Modulus (Type 1, 0.125", 0.2"/min)	ASTM D638	2,400 MPa (350,000 psi)
Tensile Elongation (Type 1, 0.125", 0.2"/min)	ASTM D638	4% (4%)
Flexural Strength (Method 1, 0.05"/min)	ASTM D790	61 MPa (8,800 psi)
Flexural Modulus (Method 1, 0.05"/min)	ASTM D790	2,300 MPa (336,000 psi)
IZOD Impact, notched (Method A, 23 °C)	ASTM D256	139 J/m (2.6 ft-lb/in)
IZOD Impact, un-notched (Method A, 23 °C)	ASTM D256	283 J/m (5.3 ft-lb/in)

Thermal Properties ²	Test Method	Value
Heat Deflection (HDT) @ 66 psi, 0.125" unannealed	ASTM D648	96 °C (204 °F)
Heat Deflection (HDT) @ 264 psi, 0.125" unannealed	ASTM D648	82 °C (180 °F)
Vicat Softening Temp. (Rate B/50)	ASTM D1525	99 °C (210 °F)
Coefficient of Thermal Expansion (flow)	ASTM E831	8.82x10-05 mm/mm/°C (4.9x10-05 in/in/°F)
Coefficient of Thermal Expansion (flow)	ASTM E831	8.46x10-05 mm/mm/°C (4.7x10-05 in/in/°F)
Glass Transition (Tg)	DSC (SSYS)	108 °C (226 °F)
Melting Point		Not Applicable ³ (Not Applicable ³)

Electrical Properties ⁴	Test Method	Value Range
Volume Resistivity	ASTM D257	1.5x1014 - 6.0x1013 ohm-cm
Dielectric Constant	ASTM D150-98	2.9 - 2.7
Dissipation Factor	ASTM D150-98	.00530051
Dielectric Strength	ASTM D149-09, Method A	370 - 80 V/mil

ABS-M30i



/			
Other ²		Test Method	Value
Specific Gravity		ASTM D792	1.04
Specific Gravity		ASTM D785	109.5
Food Safety Certification		NSF 51	Certified
System Availability	Layer Thickness	Support Structure	Available Colors

System Availability	Layer Thickness Capability	Support Structure	Available Colors
Fortus 450mc [™] Fortus 900mc [™]	0.013 inch (0.330 mm) 0.010 inch (0.254 mm) 0.007 inch (0.178 mm) 0.005 inch (0.127 mm) ¹⁵	Soluble Supports	□ Ivory

The information presented are typical values intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes. End-use material performance can be impacted (+/-) by, but not limited to, part design, end-use conditions, test conditions, etc. Actual values will vary with build conditions. Tested parts were built on Fortus 400mc™ @ 0.010" (0.254 mm) slice. Product specifications are subject to change without notice.

The performance characteristics of these materials may vary according to application, operating conditions, or end use. Each user is responsible for determining that the Stratasys material is safe, lawful, and technically suitable for the intended application, as well as for identifying the proper disposal (or recycling) method consistent with applicable environmental laws and regulations. Stratasys makes no warranties of any kind, express or implied, including, but not limited to, the warranties of merchantability, fitness for a particular use, or warranty against patent infringement.

*It is the responsibility of the finished device manufacturer to determine the suitability of all the component parts and materials used in their finished products.

¹Build orientation is on side long edge.

²Literature value unless otherwise noted.

³Due to amorphous nature, material does not display a melting point.

4All Electrical Property values were generated from the average of test plaques built with default part density (solid). Test plaques were 4.0 x 4.0 x 0.1 inches (102 x 102 x 2.5 mm) and were built both in the flat and vertical orientation. The range of values is mostly the result of the difference in properties of test plaques built in the flat vs. vertical orientation.

⁵ 0.005 inch (0.127 mm) layer thickness not available for Fortus 900mc

For more information regarding biocompatibility of our FDM materials please visit this page: Biocompatibility of our FDM materials

Stratasys Headquarters

7665 Commerce Way, Eden Prairie, MN 55344 +1 800 801 6491 (US Toll Free)

+1 952 937-3000 (Intl)

+1 952 937-0070 (Fax)

1 Holtzman St., Science Park, PO Box 2496 Rehovot 76124, Israel +972 74 745 4000

+972 74 745 5000 (Fax)

stratasys.com

ISO 9001:2015 Certified

